



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Use in your Country or Municipality

Tripp Lite Healthcare Product Specialist

Safe-IT Medical-Grade Power Strip, UL 1363, 6x Hospital-Grade Outlets, Antimicrobial, 6 ft. Cord

MODEL NUMBER: PS-606-HG



Medical-grade power strip with patented antimicrobial coating and 6 ft. cord provides safe, versatile power distribution.

Description

The PS-606-HG Medical-Grade Power Strip supplies power outside of patient-care vicinities, such as administrative areas or in resident rooms of long-term care facilities that do not use line-operated electrical equipment for diagnostic, treatment or monitoring purposes. Compliant with UL 1363 specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and six NEMA 5-15R-HG hospital-grade outlets.

The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

A built-in resettable 15A circuit breaker controls power to all outlets and protects the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The six-foot (1.8-meter) cord reaches convenient power sources.

Keyhole mounting tabs and flanges make installing this power strip easy. The all-metal housing ensures safety and is guaranteed to last a long time in demanding surroundings.

Features

Power Distribution Outside of Patient-Care VicinitiesIdeal for use in administrative areas and resident rooms with no line-operated electrical equipment for diagnostic, treatment or monitoring purposes120V, 50/60 Hz power strip complies with UL 1363 specifications

Exclusive, Patented Antimicrobial ProtectionSilver ionic powder coating is 99.9% effective in inhibiting the growth of bacteriaPatented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environmentsCoating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution6 NEMA 5-15R-HG hospital-grade outlets provide consistent powerRugged, all-metal housing for long life in demanding environments

Highlights

- Patented antimicrobial coating is 99.9% effective in inhibiting the growth of bacteria
- Complies with UL 1363 specifications
- 6 ft. (1.8 m) cord with NEMA 5-15P-HG hospital-grade plug
- Features 6 NEMA 5-15R-HG hospital-grade outlets

Package Includes

- PS-606-HG UL 1363 Medical-Grade Power Strip
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Premium Safety Features Resettable 15A circuit breaker protects against dangerous overloads
Switchless design prevents accidental shut-off
Ready to Use Right Out of the Box Built-in keyhole mounting tabs and flanges make the PS-606-HG easy to install on a variety of surfaces

Specifications

OVERVIEW	
UPC Code	037332121035
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Antimicrobial Coating	Yes
Color (AC Line Cord)	White
Included Mounting Accessories	Keyhole mounting tabs and flanges



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17
Material of Construction	Metal
Outlets Measurement (Center to Center)	38.7mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	6.10 x 14.73 x 36.07
Shipping Dimensions (hwd / in.)	2.40 x 5.80 x 14.20
Shipping Weight (kg)	1.18
Shipping Weight (lbs.)	2.60
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	1.09
Unit Weight (lbs.)	2.40
SPECIAL FEATURES	
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Canada	cUL (Series Number: AGIB12015SL)
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>