

Specification Sheet

Part Number: 151-01245



Easy assembly without the need of a tool.

Disc covers mounting hole and minimizes ingress of dust, dirt and water.

Standard geometry fits common 6.5 mm hole size

Article Number	151-01245
Type	PLUGFTOVAL
Color	Black (BK)
Quantity Per	carton
Product Description	Developed especially for the automotive industry in applications including trunks, doors, wheel housings and dash panels.
Short Description	Push Pin, Mounting Hole Dia. 6.2-7.0x12.2-13.0mm, PA66HIRHS, Black, 7000/carton
Global Part Name	PLUGFTOVAL-PA66HIRHS-BK

Length L (Imperial)	0.93
Length L (Metric)	23.6
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.69
Width W (Metric)	17.63
Height H (Imperial)	0.61
Height H (Metric)	15.6
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 " 0.25 x 0.50 " 0.25 x 0.50 " 0.27 x 0.47
Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm 7.0 x 12.0 mm 6.5 x 13.0 mm 6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	13.0

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	7000
Package Quantity (Metric)	7000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)