







NOTES:

1. ALL PARTS ARE BULK PACKED.
2. CONTACTS SHIPPED UNASSEMBLED
3. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASSEMBLY P/N	CONTACT QTY.		CABLE O.D. RANGE
	#16	#26	
W8A80-8SG-P-513	2	6	.13-.15 [3.3-3.8]
W8A80-8SG-P-516			.16-.18 [4.1-4.6]
W8A80-8SG-P-519			.19-.21 [4.8-5.3]
W8A80-8SG-P-522			.22-.25 [5.6-6.3]
W8A80-8SG-P-526			.25-.27 [6.4-6.9]
W8A80-8SG-P-528			.26-.285 [6.6-7.2]

**MATING FACE**CABLE-TO-CABLE CONNECTOR
MAT'L: UV PBT, BLACK**WIRING END****SHOWN ASSEMBLED**
FOR CUSTOMER REFERENCE ONLY

DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

A	MA	07-20-20	RELEASED PER PDR 16014-10
	PNK	01-18-18	PDR16014
REV.	INIT.	DATE	DESCRIPTION
			ORIG. DRAWN BY: DATE: PNK 01-18-18
			CHECKED BY:
			APPROVED BY:
			TITLE: CABLE-TO-CABLE ASSEMBLY 2-16 + 6-26 SOCKET CONTACTS, CRIMP INSTA-CLICK™ MINI-CON-X POWER/SIGNAL CUSTOMER: STANDARD PRODUCT
	NTS	SIZE B	SCALE NTS SIZE B SHEET 1 OF 1
			FILE: W8A80-8SG-P-5XX DIRECTORY: SLW
			PART NUMBER: W8A80-8SG-P-5XX REV A

RoHS COMPLIANT

601 E. WILDWOOD VILLA PARK, IL 60181

ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.
UNLESS OTHERWISE SPECIFIED
TOLERANCES:
3 PLACE DECIMALS ±.010
ANGLES ±1°
FRACTIONS 1/16
► = CRITICAL CHARACTERISTIC
FLAG PER SPEC. XXXX