




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-25-302515	17JAN2025	TR	RCG


Note:
X= 1,2,3,4,5,6
YYWWD
YY=YEAR
WW=WEEK
D=1 for Sunday -
7 for Saturday



LED Specification:


	Wave Length (nm)		
	Min.	Avg.	Max.
GREEN	565	567	570
ORANGE	600	605	610

NOTE:
1.Housing:Glass Filled PA46 BLACK(RoHS).
2.Insert:Glass Filled PBT BLACK(RoHS).
3.Shielding:C2680 T=0.20mm.
4.Contact:C5210 T0.35*0.44mm Phosphor Bronze.
5.Led1:GREEN/ORANGE.
6.Led2:GREEN/ORANGE.
※Operating Temperature:-40℃ to +85℃.
※MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68,SUBPART F.
※The Dimension with ▲ marked is the key dimension.



RECOMMENDED P.C.B LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.05)

GF	2497307-6
0.0762 μm [3μ"]	2497307-5
0.1524 μm [6μ"]	2497307-4
0.381 μm [15μ"]	2497307-3
0.762 μm [30μ"]	2497307-2
1.27 μm [50μ"]	2497307-1
GOLD PLATING THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TARUN, R 21NOV2024		TE Connectivity								
DIMENSIONS: mm [INCHES]		CHK RAMESH, KIVADER 22NOV2024										
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD RAGHAVAN, CG 22NOV2024		NAME RJ45 W/O MAGNET 2X6 1G LED							
			PRODUCT SPEC 108-161621									
			APPLICATION SPEC 114-161218		SIZE A2		CAGE CODE 00779		DRAWING NO C-2497307		RESTRICTED TO —	
	MATERIAL —		FINISH —		WEIGHT —							
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 of 1		REV A				