



**Part Number :** [15975161](#)

**Product Description :** Mini-Fit TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 16 Circuits, Black

**Series Number :** 30067

**Status :** Active

**Product Category :** Connector Housings

**Engineering Part Number :** 30067-16A2



---

## Documents and Resources

### Drawings

[015975161\\_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PK-30067-001-001.pdf](#)

[PS-45750-001-001.pdf](#)


[PS-5556-003-001.pdf](#)

[TS-30067-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	30067
Description	Mini-Fit TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 16 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current derating information. Connector Position Assurance
Product Name	Mini-Fit TPA
UPC	800754202275

### Agency

CSA	LR19980
-----	---------

UL	E29179
----	--------

## Physical

Circuits (maximum)	16
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	4.444/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mini-Fit TPA Dual Row Vertical Headers	<a href="#">30069</a>
Mini-Fit TPA Dual Row Right-Angle Headers	<a href="#">30070</a>

### Use with Part(s)

Description	Part Number
Mini-Fit TPA Keys	<a href="#">30072</a>
Mini-Fit Connector Position Assurance Key	<a href="#">30071</a>
Mini-Fit Female Crimp Terminals	<a href="#">5556</a>
Mini-Fit Plus Female Crimp Terminals	<a href="#">45750</a>

---

This document was generated on Apr 23, 2026