

Electrical Characteristics

- Fiber Code - T
- Performance Option Code - 90
- Optical Fiber Type - 50 Multimode
- ISO/IEC 11801 Nomenclature – OM4
- Wavelength (nm) - 850/1300
- Maximum Attenuation (dB/km) - 3.0/1.0
- Minimum Over Filled Launch (OFL) - 1500/500 MHz km
- Minimum Effective Modal - 4700/— (MHz km)
- Serial 1 Gigabit Ethernet Distance (m) - 1000/600
- Serial 10 Gigabit Ethernet Distance (m) - 550/—

Physical Characteristics

- Fiber Count - 2
- Nominal Weight kg/km (lb/1000ft) - 3.4 (2.3)
- Nominal Outside Diameter mm (in) - 2.0 (0.08)
- Minimum Bend Radius Loaded cm (in) - 3.0 (1.2)
- Minimum Bend Radius Installed cm (in) - 1.0 (0.4)
- Maximum Tensile Loads Short-Term N (lbf) - 220 (48)
- Maximum Tensile Loads Long-Term N (lbf) - 66 (15)
- Storage Temperature - -40°C to 70°C
- Installation Temperature - 0°C to 60°C
- Operation Temperature - 0°C to 70°C
- Approvals - NEC, OFNP, CSA FT-6, ICEA S-83-596

Product Support

Downloads

- Download the [technical specifications](#)

Info

About Us
Order History
Where To Buy
More ▾

Service

Contact Us
OEM Solutions
Tech Support
More ▾

Resources

Connector Guides
ConnectXpress
Drivers & Manuals
More ▾

Have A Question?

Get help with [Chat](#)
Call C2G **800.506.9607**



United States | Europe +

Copyright © 2019 C2G. All Rights Reserved

