



Part Number : [988171045](#)

Product Description : NSCC Single Part, Unsealed, 1.50mm, Female Housing, 3.33mm Pitch NSCC, Wire-to-Wire, 4 Circuits, Green

Series Number : 98817

Status : Active

Product Category : Connector Housings

Engineering Part Number : 010205325



Documents and Resources

Drawings

[988171045_sd.pdf](#)

[PK-31301-635-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[988210001-AS-CH-001.pdf](#)


[988210001-PS-CH-001.pdf](#)

[PS-98821-001-001.pdf](#)

[988175726-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Connector Housings
Series	98817
Description	NSCC Single Part, Unsealed, 1.50mm, Female Housing, 3.33mm Pitch NSCC, Wire-to-Wire, 4 Circuits, Green
Application	Power, Wire-to-Wire
Product Name	NSCC
UPC	822348760947

Physical

Circuits Detail	4 x 1.5mm female terminals
Circuits (maximum)	4
Color - Resin	Green
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes

Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	2.480/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	3.33mm
Pitch - Termination Interface	3.33mm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +100°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
NSCC 3.33mm Pitch Male Pin Connector, Non-Sealed, 4 Circuits, Green	<u>988221045</u>

Use with Part(s)

Description	Part Number
NSCC Receptacle Terminal Size 1.5, Wire Size 0.22 up to 0.44mm ²	<u>988971109</u>
NSCC Receptacle Terminal Size 1.5, Wire Size 0.49 up to 0.94mm ²	<u>988971119</u>
NSCC Receptacle Terminal Size 1.5, Wire Size 0.95 up to 1.87mm ²	<u>988971129</u>

Application Tooling

Global

Description	Part Number
Extractor Tool for Unsealed Receptacle Connectors	<u>638133800</u>

This document was generated on Jan 04, 2026