



REV.	DATE	DESCRIPTION
NC	07/26/00	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	 Connex Corporation			
1 BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	DRAWN G.R.S.	07/26/00				
2 INSULATOR	TEFLON	NATURAL		CHECKED		TITLE BNC PANEL DIRECT SOLDER JACK (FOR .085", .086" SEMI RIGID CABLE)			
3 CONTACT PIN	PHOS. BRONZE	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	ISSUED		SIZE	FSCM NO.	DWG. NO.	REV.
4 SOLDER NUT	BRASS	GOLD				A	99001	112616.DWG	NC
5									
6									
7									
8			DO NOT SCALE DRAWING			SCALE NA	PART NO. 112616	SHEET 1 OF 1	