



PRODUCT NUMBER	PITCH
HWxx50x400J0G	5.08 mm



Material:

- Item①Top body:Thermoplastic(UL94V-0)
- Item②Bottom body:Thermoplastic(UL94V-0)
- Item③Terminal lever:Thermoplastic(UL94V-0) Orange(RAL2011/P)
- Item④Spring clamp:Stainless Steel
- Item⑤Female contact:PhBz (CuSn) Tin plated

Electrical cULus

- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:9-10mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C

Dimension

DIM A	N×5.08
DIM B	(N-1)×5.08

N=Number of poles

POLES	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-16p	±0.30
17p-24p	±0.40

PART NO.: HW xx 50 x 4 00J0 G

Solid block
No. of poles
02 2 poles
03 3 poles
...
24 24 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	angles	TERMINAL BLOCK			
					X.±0.5	MM	title			
					X.X±0.3		TERMINAL BLOCK			
					X'±1"		SPRING CLAMP, PLUGGABLE PLUG			
						scale	CONTACT IN THE MIDDLE SIDE			
			dr	EVIN ZHONG	051514		dwg no		sheet 1 of 1	size
			enr	EVIN ZHONG	051514		HWxx50x400J0G			A4
			chr	HANKE FENG	051514					
			appd	SHI JUN	051514		type		CUSTOMER	Drawing
sheet index	revision	A		1						