







CONTACT DETAIL

- CONTACT PLATING
MATING AREA: 0.76 MICRO METERS MINIMUM GOLD PLATING
TERMINATION AREA: 0.05 MICRO METERS MINIMUM GOLD PLATING
UNDERPLATING: NICKEL PLATING
- APPLICABLE HOOD
HDR-E50LPH
- MATING CONNECTOR
HDR-EC50LFDT () () +
- SPECIFICATION
RATED CURRENT 0.5A
RATED VOLTAGE 125V AC (r. m. s.)

					4	SPACER	PA9T (GF)	1	——	UL94V-0 BLACK
					3	INSULATOR	PBT (GF)	1	——	UL94V-0 BLACK
					2	SHELL	STEEL	1	NICKEL PLATING	——
					1	MALE CONTACT	PHOSPHOR BRONZE	50	NOTE #1	——
LTR.	DATE	BY	REV. DESCRIPT		No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
DATE Mar. 13, 2006		SCALE 3 / 1		UNIT mm (INCH)	3RD. A. P	HONDA TSUSHIN KOGYO CO., LTD.				
APP. DATE&REV.										
DR.		DE.		CHK.	CHK.	APP.	NAME		0.8mm SPACING SHIELDED MALE CABLE CONNECTOR	
Y. KATO		Y. KATO		——	——	H. EBIHARA	PART NO.		HDR-E50MSG1+	
									REV.	