
Part Number : 640014300
Product Description : PremiumGrade Hand Crimp Tool for Avikrimp Fully Pre-Insulated and Insulated Quick Disconnect Flags, 22-14 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools
Engineering Part Number : RHT-AFIFG



Documents and Resources

Tooling Specifications

ATS-640014300-001.pdf
TM-640160065-001.pdf
TM-640160065CN-001.pdf
TM-640160065DE-001.pdf
TM-640160065SP-001.pdf
TM-640160065FR-001.pdf
TM-640160065IT-001.pdf
TM-640160065JP-001.pdf
TM-640160065KR-001.pdf
TM-640160065MY-001.pdf
TM-640160065PL-001.pdf
TM-640160065RU-001.pdf
TM-640160065SK-001.pdf
TM-640160065TH-001.pdf
TM-640160065VN-001.pdf
TM-640160065TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant

Downloaded from Arrow.com.

Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for Avikrimp Fully Pre-Insulated and Insulated Quick Disconnect Flags, 22-14 AWG
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822348077434

Downloaded from Arrow.com.

Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	643.700/g

Applicable Parts

Description	Part Number
Avikrimp Quick Disconnect, Female Flag, for 22-18 AWG (0.80-0.35mm^2) Wire, Tab 6.35 x 0.81mm, Red, Carton	190060001
Avikrimp Quick Disconnect, Female Flag, for 22-18 AWG (0.80-0.35mm^2) Wire, Tab 4.75 x 0.51mm, Red, Carton	190060005
Avikrimp Quick Disconnect, Female Flag, for 22-18 AWG (0.80-0.35mm^2) Wire, Tab 4.75 x 0.81mm, Red, Carton	190060008
Avikrimp Quick Disconnect, Female Flag, for 16-14 AWG (2.00-1.30mm^2) Wire, Tab 6.35 x 0.81mm, Blue, Carton	190060011

Downloaded from Arrow.com.

Avikrimp Quick Disconnect, Female Flag, for 16-14 AWG (2.00-1.30mm^2) Wire, Tab 4.75 x 0.51mm, Blue, Carton	190060015
Avikrimp Quick Disconnect, Female Flag, for 16-14 AWG (2.00-1.30mm^2) Wire, Tab 4.75 x 0.81mm, Blue, Carton	190060017

Downloaded from Arrow.com.