


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/19/10	


APPROVED: _____

DATE: _____ TITLE: _____










RECOMMENDED PANEL HOLE



SPECIFICATIONS:
Material:
Insulator: Thermoplastic. rated UL94V–2
Insulator color: Natural
Contact: Copper Alloy
Electrical:
Current rating: 13A
Voltage rating: 600V
Insulation resistance: 1,000 Mohms min.
Withstand voltage: 5000V AC/ minute
Temperature range: –55°C to +105°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	DY	11/19/10
CHECKED		
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .250 [6.35] WIRE TO WIRE, FEMALE, 3 POLES

SIZE	PART NO.	REV.
X	DME-F-03	-

REF:	SCALE:	SHEET
S00004T	NTS	1 OF 1

Downloaded from Arrow.com.