

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1062840005

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

CXP Optical Cable Assembly (iPass+), MTP-to-MTP, Multimode, 50/125µm, Round Cable Assembly, Straight Boot, Standard Bandwidth, OFNR, Cable Diameter 3.80mm, Cable Length 5.00m



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Fiber Optic Assemblies
Series	106284
Boot Type	Straight
Connector to Connector	MTP-to-MTP
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Name	CXP, iPass+, MTP
UPC	883906549985
Physical	
Cable Length	5.0m
Cable Size	3.80mm
Fiber (Core/Cladding)	50/125µm
Net Weight	96.300/g
Single Ended	No
Wire/Cable Type	Fiber Optic, Round
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-106284-0001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

106284 Series

Mates With

CXP Optical Transceivers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION