



Pushing Performance
Since 1945

InduCom9 MVB/WTB female PL2 M3 set



Image is for illustration purposes only. Please refer to product description.

Part number	66 63 009 5222
Specification	InduCom9 MVB/WTB female PL2 M3 set
HARTING eCatalogue	https://harting.com/66630095222

Identification

Category	Connectors
Series	D-Sub
Element	Bus interface
Specification	MVB/WTB interface

Version

Termination method	Cage-clamp termination
Gender	Female
Size	D-Sub 1
Number of contacts	9
Version	Top entry
Number of cable entries	2
Cable entry	2x
Locking type	Hexagonal screw Thread M3
Pack contents	Blind plate Crimp flange Crimp ferrule

Technical characteristics

Conductor cross-section	0.08 ... 0.5 mm ²
Conductor cross-section [AWG]	AWG 28 ... AWG 20
Rated voltage	<50 V AC <75 V DC
Stripping length	5 ... 6 mm



Pushing Performance
Since 1945

Technical characteristics

Tightening torque	≤0.4 Nm Locking screw ≤0.3 Nm cover screw
Limiting temperature	-40 ... +85 °C
Performance level	2
Degree of protection acc. to IEC 60529	IP40
Test voltage $U_{r.m.s.}$	0.5 kV

Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled
Material (contacts)	Copper alloy
Surface (contacts)	Selectively gold plated
Material (hood/housing)	Zinc die-cast
Length	61.7 mm
Width	31.6 mm
Height	14.8 mm
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	10
Net weight	82.32 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140216563



Pushing Performance
Since 1945

Commercial data

eCl@ss	27440302 D-Sub-Connector
ETIM	EC001132
UNSPSC 24.0	39121403