
Product Line

Single Pair Ethernet
ZConnect
Ceres
Accessory
Large Size
Macro Size
Middle Size
Mini Size
Others (GBD)
Others (MAB)
Others (PLD)
Standard Size
X-Lok
M Series
FLOS & FLOS+
Power
RBL
HS-Lok
NMEA 2000
Heavy Duty Shielded
RJ
USB
SSL
HDMI
DVI
Fiber Optic
RF
Cable Joiner
Cable Gland
Pressure Relief Vent
LED Light Guide
D-Sub





ACD-12PMMS-SC7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL1977

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



Ceres, Middle Size...
1CD-12BFFM-SL6A01
-20°C ~ +80°C



Ceres, Middle Size...
1CD-12BFFM-SL6A02
-20°C ~ +80°C



Ceres, Middle Size...
1CD-12BFFM-SL6A03
-20°C ~ +80°C



Ceres, Middle Size...
1CD-12BFFM-SL6A04
-20°C ~ +80°C

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current 5A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 12
Connector Gender Male	Backshell Circular
Mating Style Screw Thread	IP Rating IPX7
Assembly Style Solder	

More Options

People Also Bought

Downloaded from Arrow.com.