Part Number : 1301800333
Product Description : MAX-LOC O-Ring, 3/4" NPT
Series Number : 130180
Status : Active
Product Category : Cable Grips
Engineering Part Number : 00-0822



Documents and Resources

Drawings

1301800333_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130180
Description	MAX-LOC O-Ring, 3/4" NPT
Product Name	MAX-LOC
Type	O-Ring
UPC	78678802155

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	N/A
Cable Diameter	N/A
Color - Grommet	N/A
Eye Type	N/A
Gender	N/A
Material - Body	Neoprene
Material - Grip	N/A
Mesh Length	N/A
Net Weight	0.907/g
Number of Holes	1
O-Ring	Yes
Thread Size	3/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
Strain Relief Grips	130096
Strain Relief Grips	130097

Downloaded from Arrow.com.

MAX-LOC Strain Relief Grips	130098
MAX-LOC Strain Relief Grips and Accessories	130099

Downloaded from Arrow.com.