




+ RELAYS, CONTACTORS & SWITCHES

PUSHBUTTON SWITCHES



✓ Active

TE CONNECTIVITY (TE)

**AV19 SPM 5A SPOT LED RED 12V**

Alcoswitch | Alcoswitch AV

AV1910D312Q04

TE Internal Number: 2213765-5

EU RoHS Compliant

EU ELV Compliant

**Configuration (Pole-Throw)** Single Pole - Single Throw

**Number of Actuators** Single

**Actuator Profile** Flush

**Bushing Style** Threaded

**Illuminated** Yes

 **PRODUCT DRAWING**  
English

 **3D PDF**

## DOCUMENTATION

Product Drawings

**ANTI-VANDAL SWITCH 19mm SPOT LED**

PDF

English

CAD Files

**3D PDF**

PDF

3D

**Customer View Model**

2D\_DXF.ZIP

English

**Customer View Model**

3D\_IGS.ZIP

English

### Customer View Model

3D\_STP.ZIP

English

---

Agency Approvals

UL Report

### Anti Vandal Switches

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

#### Product Type Features

**Illuminated** Yes

**Actuator Style** Round

**Product Type** Switch

**Switch Type** Pushbutton

**Dust Proof** Yes

---

#### Configuration Features

**Configuration (Pole-Throw)** Single Pole - Single Throw

**Number of Actuators** Single

**Snap Action** Without

**Support Bracket** Without

**Tactile** No

**Operating Function** Momentary

**ESD Grounding Terminal** Without

**Detent Style** Audible

---

#### Electrical Characteristics

**Voltage Rating (VAC)** 250

---

#### Body Features

**Actuator Profile** Flush

**Bushing Style** Threaded

**Case Material** PBT

---

#### Contact Features

**Contact Current Rating (A)** 5

**Contact Plating** Silver

---

#### Termination Features

**Termination Type** Wire Lugs

---

Mechanical Attachment

**Mounting Type** Panel

**Mounting Angle** Vertical

---

Housing Features

**Process Sealed** Yes

---

Dimensions

**Bushing Length (in)** 19

Statement of Compliance

**Statement of Compliance**

PDF

---