
Part Number : 191930118
Product Description : VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Plated, Tape and Reel
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : C-330-14T



Documents and Resources

Drawings

191930118_sd.pdf

Specifications

PS-19902-011-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Plated, Tape and Reel
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753039322

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	1.965/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/4" (M6)

Downloaded from Arrow.com.

Temperature Range - Operating	-50° to +149°C
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	10, 12
Wire Size mm^2	4.00-6.00

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	638851000
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270088

This document was generated on Sep 02, 2026

Downloaded from Arrow.com.