


XZG425



Item number 66.9407-*

Highly flexible, with stackable Ø 4 mm MULTILAM plugs on both ends with protective collar and retractable sleeve to prevent accidental touching. Especially suitable for connecting electrical devices not (yet) equipped with safety sockets.

Technical data	
Diameter of plug system	4 mm
Rated Values	600 V, CAT II, 32 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25 27 28
Optional color(s)	20 26 29
Lead lengths <input type="text"/>	025; 050; 100; 150; 200 cm
Lead insulation	PVC
Lead cross section	2,5 mm ²
Test accessory acc. to	IEC EN 61010-031
User-Information	I074
Remarks	Other color and/or length combinations available on request.
Approvals	CE

