

RJ45 Plugs for Solid / Stranded Conductor 4-pair Cat5e Cable, 10-Pack, TAA

MODEL NUMBER: **N030-010**



Highlights

- RJ45 Plug for Solid Conductor 4-pair Cat5e cable
- 50 Micron Gold Contacts
- Can be used for Solid or Stranded Conductor Wire

Package Includes

10pc RJ45 Solid Conductor RJ45 Plugs

Description

10-Pack of RJ45 Modular plugs for use on Solid Conductor Cat5e cable, N022-01K-GY or Zero-Skew cable P524-01K (can be used for Stranded wire as well). Contacts are 50-micron Gold for optimum signal transmission. For stranded conductor Cat5e RJ45s, see N031-050.

Features

- For use with Cat5e Solid (or Stranded) Conductor 4-pair cable
- Works with most RJ45 Crimp Tools (excluding AMP)
- 50 Micron Gold Contacts

Specifications

OVERVIEW	
UPC Code	037332147578
Product Type	RJ45 Plug
Technology	Cat5/5e
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.25 x 3.90 x 5.70
Shipping Dimensions (hwd / cm)	0.64 x 9.91 x 14.48
Shipping Weight (lbs.)	0.05



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	0.02
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.