Data sheet

HTI 15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for insulated connectors
cable lugs, terminal pins, parallel and serial connectors, plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

Version	Pressing tool, Tool for insulated cable connectors, 0.5mm², 2.5mm², Double crimp
Order No.	9014400000
Type	HTI 15
GTIN (EAN)	4008190159412
Qty.	1 items

Downloaded from Arrow.com.

Data sheet

HTI 15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	440.68 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for insulated connectors, 0.5-2.5 mm²	Version	Mechanical, without interchangeable inserts

Description of contact

Type of contact	Insulated connector	Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 21	Crimping range, max.	2.5 mm²
Crimping range, min.	0.5 mm²		

tool data crimping

Wire end ferrules cross-section, max.	2.5 mm²	
Crimping type/profile	Double crimp	
Crimping station	Crimping station number	1
	Conductor cross-section, min.	0.5 mm²
	Conductor cross-section, max.	1.5 mm²
	Conductor cross-section AWG, min.	21 AWG
	Conductor cross-section AWG, max.	16 AWG
	Colour of crimping station	Red
	Crimping station number	2
	Conductor cross-section, min.	1.5 mm²
	Conductor cross-section, max.	2.5 mm²
	Conductor cross-section AWG, min.	16 AWG
	Conductor cross-section AWG, max.	14 AWG
	Colour of crimping station	Blue

Important note

Product information	Not suitable for solid conductors. Insulation on the contact is pressed conically.

Classifications


ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.