






Insert to be used for hoods with part numbers:

09 67 OXX 0424
 09 67 OXX 0425
 09 67 OXX 0434
 09 67 OXX 0435

XX = 09, 15, 25 or 37

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	Screw M3 for D-Sub hoods 9 to 37 poles	Maßstab/ Scale 6:1
			Detail.	09/10/09	PK			
			Insp.					
			Stand.					
EC00971	09/10/09	PK	HARTING EURL F-95972 Paris				TB 09 67 002 9102	Blatt/ Page 1 / 1
Mod.	Dat.	Name					Sub.	