
Part Number : 354076502
Product Description : 2.28mm Terminal, Female, 0.85-1.25 AVSS, 0.25mm Thickness, Pre-Tin Plated
Series Number : 35407
Status : Obsolete
Product Category : Crimp Terminals



Documents and Resources

Specifications

PS-35365-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	35407
Description	2.28mm Terminal, Female, 0.85-1.25 AVSS, 0.25mm Thickness, Pre-Tin Plated
Product Name	N/A
UPC	756054280447

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.460/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size (AWG)	16, 18
Wire Size mm^2	N/A

Obsolete

Mates With / Use With

Mates with Part(s)

Description	Part Number
Tab Terminals	35420

Use with Part(s)

Description	Part Number
Automotive Horn Female Housings	35825

Downloaded from Arrow.com.

This document was generated on Sep 02, 2026

Obsolete

Downloaded from Arrow.com.