

OA300ST Series



432x203x44.5mm
(17"x 8"x1.75")



- Lighted rocker switch
- Resettable circuit breaker.
- Unit slides in to any standard 19" rack.
- Tray features 3 high performance sealed ball bearing fans.
- Black wrinkle finish.
- Operating temperature: -40 to +75 degrees C

Part Number	OA300ST-120	OA300ST-230
No. of Fans	3	3
Bearing System	Dual Ball Bearing	Dual Ball Bearing
Nominal Voltage (60Hz)	115 VAC	230 VAC
Input Power	45 Watts	45 Watts
Rated Speed (RPM)	3000	3000
Airflow (CFM)	310	310
Noise Level (dB)	53	53
Life Expectancy	60,000 hrs (25C)	60,000 hrs (25C)
Connection	2M Modular Power Cord	2M Modular Power Cord