

Technical data sheet

Article number:
301-10021

SA47-LA-7.5/1.65

Product Group	4:1 Heat shrink tubing - 1.2m lengths
Product Family	SA47-LA - standard wall adhesive lined for perfect corrosion protection
Material	Polyolefin, cross-linked (PO-X)
Colour	Transparent (CL), Black (BK)
Adhesive	EVA hot melt adhesive
Behaviour at Heat Shock	not cracking
Dielectric Strength	20 kV/mm
Elongation at break (min.)	450 %
Flammability	FMVSS 302
Heat Shock Test	4h/225°C
Longitudinal Change After Shrinkage	-10% max.
Min. Shrink Temperature - °C	+130 °C
Operating Temperature	-40 °C to +125 °C
Package Content	1.2 m
Package Content packed in	pcs.
Recov. Ø d max.	1.65 mm
Shrink Ratio	4:1
Supplied Ø D min.	7.5 mm
Tensile Strength	14 MPa
Wall (WT)	1.4 mm
Water Absorption	0.5 %

HF ✓

RoHS ✓