



# PATRIOT® Series, 6-Ton Scissor Action, BG/D3 Crimp Jaw, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy  
Catalog # PAT500SJ6L5

6T Scissor, BG/D3, 5Ah, AC, HC



## Features

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

## Application

Crimping and Cutting

## Conductor

Crimping Ranges	<ul style="list-style-type: none"> <li>• Copper: #10 sol. - 500 kcmil</li> <li>• Copper Flex: #8 AWG - 350 kcmil</li> <li>• Aluminum: #14 sol. - 350 kcmil</li> <li>• ACSR: #14 sol. - 4/0 AWG</li> </ul>
-----------------	---

## Current

Operating Voltage	18 VDC
-------------------	--------

## Dimensions

Width	2.9 in
Weight	10.10 lb.
Height	13.4 in
Length	16.8 in
Dimensions	16.8 in x 2.9 in x 13.4 in

## Force Related

Crimp Force Capacity	6 ton
----------------------	-------

## General

Type	Crimper and Cutter
Series	PATRIOT® Series
UPC 12 Digit	621945470729
Container Type	Hard Case
Tool Type	Battery Actuated Scissor Action
UPC	621945470729
Trade Name	PATRIOT®
Die Type	W Die and X Die
Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals

## Logistics

Package Contents	Tool, BG/D3 Crimp Jaw, (2) Batteries, Charger, Lanyard, Hard Case
Minimum Pack Quantity	1

## Operational

Power Source	120V-AC Charger
Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

## Product Assets

[Catalog \[English\]](#)

