



CT50400M00, Tie, 4" Max Bundle, 50 Lb
Tensile, UV Black

By Burndy
Catalog # CT50400M00

Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength

Features


- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	Yes
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No
Military Spec Number	MS3367-2-0

Dimensions

Length	15.5 in
Dimension - Width mm	5 mm
Dimension - Width inch	0.18 in
Dimension - L Length Overall mm	362 mm
Width	0.18 in
Dimension - Length Overall inch	14.25 in
Dimension - Bundle Diameter Max inch	4



Force Related

Rating - Minimum Tensile Strength lbs	50
---------------------------------------	----

General

Color	Black
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810332856
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810332856

Logistics

Minimum Pack Quantity	5000
Carton Quantity	5000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

Catalog [\[English\]](#)