


Product Status	Production
Applications	Commercial Grade
Feature	High SpeedHigh speed signal line
Series	MMZ
Brand	TDK
Environmental Compliance	RoHS REACH Halogen Free Lead Free





Size	
Length(L)	0.60mm ±0.03mm
Width(W)	0.30mm ±0.03mm
Thickness(T)	0.30mm ±0.03mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

Electrical Characteristics	
Impedance at 100MHz	33Ω ±25%
Rated Current	200mA
DC Resistance (Max.)	700mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0003g

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



Associated Images

