



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-19-013004	26AUG2019	SR	JL
	B2	ECR-20-000836	23JAN2020	SB	JL
	B3	ECR-20-002949	02MAR2020	SR	JL
	B4	ECR-20-006986	18MAY2020	SR	DD

- 1 MATERIALS:
HOLDER: PBT ,COLOR: NATURAL;
CONTACTS: COPPER ALLOY, Au/Ni PLATING (LED INTERFACE)
2. FOR SOLID, FUSED AND STRANDED CONDUCTOR WIRE TYPES AWG 18 AND 20
3. WIRE STRIP LENGTH: 11-12mm
4. MAX. WIRE INSULATION OUTER DIA: Ø2,3mm
5. RECOMMENDED SCREW TORQUE: SEE APPLICATION SPECIFICATION 114-133107.
6. SCREWS TO BE USED: M3, #4-40
7. LED MATING ON 2 CORNERS WITH ADHESIVE TAPE 3M 9472LE 300LSE.
- 8 LAYOUTS ON SHEET 4
9. FOR COB-TO-HOLDER CROSS REFERENCE,
REFER TO APPLICATION SPECIFICATION 114-32208
- 10 PACKAGED ONE TRAY OF 20 PCS PER BOX, 10 BOXES PER SHIPPING CARTON.



PAN HEAD
SCALE 3:1



COUNTERSINK
SCALE 3:1

10

B	COUNTERSINK	5-2325807-3
B	PAN HEAD	4-2325807-3
A	PAN HEAD	4-2325807-2
B	COUNTERSINK	1-2325807-3
B	PAN HEAD	2325807-3
A	COUNTERSINK	1-2325807-2
A	PAN HEAD	2325807-2
LED LAYOUT8	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 18DEC2017	TE Connectivity			
		CHK J. LATORRE 18DEC2017				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.2 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±2°	APVD - PRODUCT SPEC 108-133062 APPLICATION SPEC 114-133107	NAME LED HOLDER, 19x19 LUMAWISE Z45 LED		
				SIZE A2	CAGE CODE 00779	DRAWING NO C-2325807
MATERIAL	1	FINISH -	WEIGHT -	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 2:1	SHEET 1	OF 4	REV B4

D

D

C


C

B



B

A

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 18DEC2017	 TE Connectivity				
		CHK J. LATORRE 18DEC2017					
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME LED HOLDER, 19x19 LUMAWISE Z45 LED -				
mm		PRODUCT SPEC 108-133062					
	0 PLC ±.0	APPLICATION SPEC 114-133107	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	1 PLC ±0.2	WEIGHT -	A200779		C-2325807		
MATERIAL	2 PLC ±0.13	CUSTOMER DRAWING	SCALE		SHEET	REV	
	3 PLC ±.		3:1		2 OF 4	B4	
	4 PLC ±.						
	ANGLES ±2°						
	FINISH						
	-						
	-						



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C. DAILY
18DEC2017

CHK
J. LATORRE
18DEC2017

APVD
-

PRODUCT SPEC
108-133062

APPLICATION SPEC
114-133107

WEIGHT
-

CUSTOMER DRAWING

NAME
LED HOLDER, 19x19
LUMAWISE Z45 LED

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2325807

RESTRICTED TO
-

SCALE
2:1

SHEET
3 OF 4

REV
B4

STE

TE Connectivity

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C

C


B

B


A

A

LED SUBSTRATE LAYOUT A
TOP SIDE OF BOARD



LED SUBSTRATE LAYOUT B
TOP SIDE OF BOARD



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C. DAILY
CHK
J. LATORRE
APVD
-

18DEC2017
18DEC2017

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.2
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±2°
FINISH
-
-

PRODUCT SPEC
108-133062
APPLICATION SPEC
114-133107
WEIGHT
-
CUSTOMER DRAWING

DWN
C. DAILY
CHK
J. LATORRE
APVD
-

18DEC2017
18DEC2017

NAME
LED HOLDER, 19x19
LUMAWISE Z45 LED
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2325807

RESTRICTED TO
-

SCALE
2:1

SHEET
4 OF 4

REV
B4