

Representative Image

Catalog No. TY100-18X-M

Description: 80N UV CABLE TIE 100MM OEM

UPC No 5415022524338

Home > Wire & Cable Management > Ty-Rap > Cable ties

Descriptors

Category	Cable ties
Special Features	The integrally formed polyamide pawl combines low insertion and high locking strength. The low profile head significantly reduces the potential for snagging during installation. Quick and easy pull through increases productivity, reduces operator fatigue. Tail with finger grip design that helps operator grasp and pull ties snugly. Sure grip tab keeps the tail from popping out while being treated, then holds it it securely for final tightening by hand or tool

Specifications

Material	Nylon/Polyamide 6.6 UV Resistant
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	180 newtons , 40 pounds

Classifications

Standard	UL E49405

Dimensions

Width	3.6mm , 0.142 in
Length	290 mm , 11.417 in
Thickness	1.2 mm , 0.047 in
Bundle Diameter	6.35 to 102 mm , 0.25 to 4.016 in

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

Downloaded from Arrow.com.