

[Find by Feature](#)
[Browse by Category](#)
[Share](#)

[Search →](#)

Enter part number or keyword

[Search Results \(0\)](#)
[Search Options](#)

Select a product type to narrow your search:

Terminal ▼

Results with your selections: --

- Blade size [mm] ▼
- Terminal family ▼
- Material ▼
- Plating ▼
- Gender ▼
- Sealed ▼
- Inside Ring Diameter [mm] ▼
- Outside Ring Diameter [mm] ▼
- Minimum Cable Core Cross Section [mm²] ▼
- Maximum Cable Core Cross Section [mm²] ▼
- Minimum Cable Diameter [mm] ▼
- Maximum Cable Diameter [mm] ▼

[Clear](#)
[Search →](#)

Female Lamp Socket Dome Clip Tin Plated Terminal, Cable Range 0.80 - 0.50 mm², Cable Insulation Range 2.41 - 2.06 mm
Part #12089845

[Question about this product?](#)

[Attributes](#)
[Documents \(3\)](#)

Part #:	12089845
Description:	Female Lamp Socket Dome Clip Tin Plated Terminal, Cable Range 0.80 - 0.50 mm ² , Cable Insulation Range 2.41 - 2.06 mm
Product Type:	Terminal
Status:	Active
Terminal family:	Lamp Socket
Series:	DOME CLIP
Gender:	Female
Sealed:	Unsealed
Material:	Carbon Steel
Plating:	Tin
Minimum Cable Core Cross Section [mm²]:	0.50
Maximum Cable Core Cross Section [mm²]:	0.80
Minimum Cable Diameter [mm]:	2.06
Maximum Cable Diameter [mm]:	2.41
Weight [g]:	1.16
ELV compliant:	Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.