

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- Middle Size
- Large Size
- ODVA
- Accessory
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



RCP-5SAMMM-TRM7B01

Operating Temperature: -20°C ~ +80°C

Transmission Speed: Cat 5e

Shielded: Plastic, Shielded

Jacket Material: PVC

Certificate: N/A

You must login first for view the price

Quantity - 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Overmolded
Shielded Plastic, Shielded	No. of Contacts N/A
Connector Gender Plug	Backshell Right Angle
Mating Style 3 Points Lock	IP Rating IP67
Assembly Style N/A	
More Options	

People Also Bought

