



**Part Number :** [1722643004](#)  
**Product Description :** Ultra-Fit Tangless  
Terminal Position Assurance (TPA), 3.50mm  
Pitch, 4 Circuits, Black  
**Series Number :** [172264](#)  
**Status :** Active  
**Product Category :** Connector Accessories



## Documents & Resources

### Drawings

[1722643004\\_sd.pdf](#)  
[1723230005-000.pdf](#)

### 3D Models and Design Files

[1722643004\\_stp.zip](#)

### Specifications

[1722640001-AS-000.pdf](#)  
[1723230003-000.pdf](#)  
[1723230001-TS-000.pdf](#)  
[1723231000-PS-CH-000.pdf](#)  
[1723231000-PS-ES-000.pdf](#)  
[1723231000-PS-JP-000.pdf](#)  
[1723231000-PS-SK-000.pdf](#)  
[PS-172323-0001-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	172264
Description	Ultra-Fit Tangless Terminal Position Assurance (TPA), 3.50mm Pitch, 4 Circuits, Black
Component Type	Terminal Position Assurance
Product Name	Ultra-Fit
UPC	191128806152

### Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.180/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +120°C

### Use with Part(s)

Description	Part Number
-------------	-------------

Ultra-Fit Tangless Receptacle Housing, 3.50mm Pitch, Single Row, 4 Circuits, Natural, Glow-Wire Capable	<u>1722564104</u>
Ultra-Fit Tangless Receptacle Housing, 3.50mm Pitch, Dual Row, 8 Circuits, Natural, Glow-Wire Capable	<u>1722584108</u>
Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 4 Circuits, Natural, Glow-Wire Capable	<u>2025694004</u>
Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 4 Circuits, Panel Mount, Natural, Glow-Wire Capable	<u>2025694104</u>
Ultra-Fit Plug Housing, 3.50mm Pitch, Dual Row, 8 Circuits, Natural, Glow-Wire Capable	<u>2169454008</u>
Ultra-Fit Plug Housing, 3.50mm Pitch, Dual Row, 8 Circuits, Panel Mount, Natural, Glow-Wire Capable	<u>2169454108</u>

---

This document was generated on Mar 22, 2025