

[Home](#) / [Products](#) / [Character Displays](#) / [Character Displays Group Detail](#)

## Part Detail: DMC-20261NY-LY-CLE-CON

► [Replacement for DMC-20261NY-LY-CIE-CLN](#)

Supporting Documentation

Other Resources

 [Specification](#) (PDF – 434K)

 [Drawing](#) (PDF – 84K)

### Application Notes

► [View all Monochrome-Character app notes \(1\)](#)

| Technical Specifications        |                                 |
|---------------------------------|---------------------------------|
| Module Type:                    | Monochrome-Character            |
| Size:                           | 3.0"                            |
| Type:                           | Transmissive                    |
| LCD Mode:                       | Yellow                          |
| Backlight:                      | Yellow-green LED                |
| Dot Format:                     | 20X2                            |
| Luminance (Cd/m <sup>2</sup> ): | 40 at backlight surface         |
| Contrast Ratio:                 | 4.5:1                           |
| Interface:                      | 8-bit parallel                  |
| Vertical Viewing Angle:         | -40/30                          |
| Horizontal Viewing Angle:       | + -30                           |
| Viewing Direction:              | 6:00                            |
| Operating Temperature (°C):     | 0 to 50                         |
| Storage Temperature (°C):       | -20 to 70                       |
| Mass (g):                       | 90                              |
| Outer Dimension (mm):           | 116.0 (W) x 37.0 (H) x 15.7 (D) |
| Status:                         | Active                          |

### Order Parts Now

KYOCERA  
DISPLAY

Order

Note: Quantity subject to change