

Part Number : [1300940450](#)


Product Description : Heavy Duty Support Grip, Double Eye, Double Weave, Closed Mesh, Cable Diameter 63.50-75.95mm (2.500-2.990"), Approximate Break Strength 4572.21kg (10080 lbs)

Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Part Number : 35430




Documents and Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Heavy Duty Support Grip, Double Eye, Double Weave, Closed Mesh, Cable Diameter 63.50-75.95mm (2.500-2.990"), Approximate Break Strength 4572.21kg (10080 lbs)
Product Name	Heavy Duty
Type	Support Grip
UPC	78678835430

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	4572.21kg (10080 lbs)
Bale Length	0.254m (10.00")
Body Style	Straight
Cable Diameter	63.50-75.95mm (2.500-2.990")
Color - Grommet	N/A
Eye Type	Double
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.965m (38.00")
Net Weight	1.000/g
Number of Holes	N/A

O-Ring	N/A
Thread Size	N/A

This document was generated on May 20, 2026