DWG. NO. SD-35301-001


SIMILAR ITEM

PROJECT NO.

STICKER OR VINYL
(MOLEX LOGO SIDE)

STOPPER

VIEW V



NOTES

1. PACKING TYPE : STOPPER & STICKER LOCKING TYPE(GENERAL)
   : VINYL & STOPPER LOCKING TYPE(FOR S/S)
2. THICKNESS : 0.6 t
3. LENGTH : 550 mm

LEGEND

35301- ** 5 *

COLOR : 0 --- NATURAL
1 --- BLACK
2 --- RED
3 --- YELLOW
4 --- BLUE

CKT (02 , 03 , 04 ....)

CKTS	ENG NO.	MAT'L NO.	Q'TY/TUBE
15	35301-155*	35301155*	10
14	-145*	35301145*	10
13	-135*	35301135*	15
12	-125*	35301125*	15
11	-115*	35301115*	15
10	-105*	35301105*	15
9	-095*	35301095*	20
8	-085*	35301085*	20
7	-075*	35301075*	25
6	-065*	35301065*	30
5	-055*	35301055*	35
4	-045*	35301045*	40
3	-035*	35301035*	50
2	35301-025*	35301025*	70

NEW RELEASED
EC NO. KOR2001-0048
DRWN: K.S.KIM (011130)
CH'K: J.K.OH
APPR: C.W.LEE

DESCRIPTION

A

REV

QUALITY SYMBOLS
MAJOR =
CRITICAL C =

GENERAL TOLERANCES: (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±0.	±.
3 PLACES	±0.	±.
2 PLACES	±0.	±.
1 PLACE	±0.4	±.

ANGULAR: ± 3 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

SCALE: NONE

DESIGN UNITS: ☒mm ☐INCH

THIRD ANGLE PROJECTION

DIMENSIONS: ☐ mm/INCH ☐ INCH/mm ☒ mm ONLY

SHT | REV

REVISE ON CAD ONLY

DRAWN BY & DATE: K.S.KIM (011130)

CHECKED BY & DATE: J.K.OH

APPROVED BY & DATE: C.W.LEE

CAD FILENAME: SD35301A.dgn

TITLE: TUBE PACKAGED FOR 5267-NAX SERIES

MOLEX INCORPORATED KOREA

MATERIAL NO.: SEE TABLE

DRAWING NO.: SD-35301-001


SHEET NO.: 1 OF 1


SIZE: A

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

MX-A4


Downloaded from Arrow.com.






RECOMMENDED P.C.BOARD HOLE DIM.
(t=1.6)

NOTES:
1. MATES WITH : 5264 SERIES.
2 APPLIES : PIN, BOTH ENDS





39.9	38.5	35	99-99-0999	5267-15A-X	35301-1550	15
37.4	36	32.5	-0998	-14A-X	35301-1450	14
34.9	33.5	30	-0997	-13A-X	35301-1350	13
32.4	31	27.5	-0996	-12A-X	35301-1250	12
29.9	28.5	25	-0995	-11A-X	35301-1150	11
27.4	26	22.5	-0994	-10A-X	35301-1050	10
24.9	23.5	20	-0993	-09A-X	35301-0950	9
22.4	21	17.5	-0992	-08A-X	35301-0850	8
19.9	18.5	15	-0991	-07A-X	35301-0750	7
17.4	16	12.5	-0990	-06A-X	35301-0650	6
14.9	13.5	10	-0989	-05A-X	35301-0550	5
12.4	11	7.5	-0988	-04A-X	35301-0450	4
9.9	8.5	5	-0987	-03A-X	35301-0350	3
7.4	6	2.5	99-99-0986	5267-02A-X	35301-0250	2
C	B	A	EDP NO.	ENG NO.	ENG NO.	NO OF CKT.
			APPLIED CONNECTOR			

ANGLE	±3°
30 OVER	±0.3
10 OVER 30 UNDER	±0.25
10 UNDER	±0.2
GENERAL TOLERANCES	

NEW RELEASED
ECN NO. KOR2006-0082
DRWN: K.S.KIM (060102)
CHK: Y.Soo.KIM
APPR: S.H.CHOI
DESCRIPTION
A
REV

QUALITY SYMBOLS
MAJOR
CRITICAL C

GENERAL TOLERANCES: (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±0.	±
3 PLACES	±0.	±
2 PLACES	±0.	±
1 PLACE	±0.	±
ANGULAR: ± °		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

SCALE 5:1
DESIGN UNITS ☐mm ☐INCH
THIRD ANGLE PROJECTION
DIMENSIONS: ☐mm/INCH ☐INCH/mm ☐mm ONLY
SHT REV
REVISE ON CAD ONLY

DRAWN BY & DATE: K.S.KIM (060102)
CHECKED BY & DATE: Y.Soo.KIM
APPROVED BY & DATE: S.H.CHOI
CAD FILENAME

TITLE:
2.5 LOW PROFILE
WAFER ASS'Y WITH COIN

MOLEX INCORPORATED

MATERIAL NO.
DRAWING NO. SD-35301-012
SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

SIZE B

KOREA MX-A3

DO NOT SCALE DRAWING
DIMENSION IN METRIC

DWG. NO.
SIMILAR ITEM
PROJECT NO.

Downloaded from Arrow.com.