








REV.	DATE	DESCRIPTION
NC	04/29/99	INITIAL RELEASE
A	07/28/06	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex			
7						DRAWN	G.R.S.	07/28/06					
6	FERRULE	COPPER	GOLD	1		CHECKED							
5	HEX NUT	BRASS	GOLD	1		ISSUED							
4	LOCK WASHER	BRASS	GOLD	1		SHEET		1 OF 1		PART NO. 132246			
3	CONTACT PIN	BER. COPPER	GOLD	1		CAD FILE		C:/132/132246.DWG				DWG. NO. 132246.DWG REV. A SIZE A SCALE NA	
2	INSULATOR	TEFLON	NATURAL	1									
1	BODY	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY									