

M12 A-cod 4-pol an/- f/- PUR 5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 35 040 0406 050
Specification	M12 A-cod 4-pol an/- f/- PUR 5m
HARTING eCatalogue	https://harting.com/21350400406050

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Female Angled
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	4
Core structure	4x 0.34 mm ²
Coding	A-coding

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead Triphenyl phosphate
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Net weight	141.861 g
Country of origin	Mexico
GTIN	5713140810426
eCl@ss	27060311 Assembled sensor actuator-line
UNSPSC 24.0	26121604