

Eaton XTCE032C10TD

Catalog Number: XTCE032C10TD

Eaton XT IEC contactor, 32A, 24-27 Vdc, 1NO, 32A, Frame C, 45 mm, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, XT IEC series, Screw terminals, Full voltage non-reversing contactor



Photo is representative

General specifications

Product Name

Eaton XT IEC contactor

EAN

4015082772741

Product Height

2 in

Product Weight

1.25 lb

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947

Catalog Number

XTCE032C10TD

Product Length/Depth

4 in

Product Width

3.5 in

Compliances

CE Marked
RoHS Compliant

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

32A

HP rating - max

3, 5, 5/ 10, 10, 20, 25 hp (1/3PH
@115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vdc

Coil voltage

24-27 Vdc

Contact configuration

1 NO

Continuous ampere rating

32 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_C 2D PDF](#)

[XTCE_C AutoCAD 2D Footprint](#)

[XTCE_C 3D Model Xchange](#)

[XTCE_C 2D Drawing Xchange](#)

Specifications and datasheets

[Global Data Sheet - XTCE032C10TD](#)

[Eaton Specification Sheet - XTCE032C10TD](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia