

Specifications

Eaton CL1108-3-50TR-R

Eaton CL1108 inductor, 50 nH, 0.28 mΩ resistance, Three-phase



General specifications

PRODUCT NAME	Eaton CL1108 inductor
CATALOG NUMBER	CL1108-3-50TR-R
UPC	051712278409
PRODUCT LENGTH/DEPTH	27 mm
PRODUCT HEIGHT	8 mm
PRODUCT WIDTH	11 mm
PRODUCT WEIGHT	9.66 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Product specifications

TYPE	Inductor
MOUNTING	SMT
PHASE	Three-phase
ISAT	10 A
PACKAGE QUANTITY	200
MATERIAL	Ferrite
CONTACT CONFIGURATION	Six-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.28 mΩ
TERMINALS	Six
INDUCTANCE	50 nH
SERIES	CL1108

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CL1108-3-50TR-R](#)

[Eaton CL1108-CLA1108 mutli-phase power inductor data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

