



Part Number : [1301020257](#)
Product Description : Safeway Phenolic Hand Lamp with 100W, Screw Release Guard with Reflector, with Side Outlet, Cord Type 16/3 SJTOW, Cord Length 7.62m (25.0')
Series Number : 130102
Status : Active
Product Category : Lamps and Lights
Engineering Number : 271UA163

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130102
Description	Safeway Phenolic Hand Lamp with 100W, Screw Release Guard with Reflector, with Side Outlet, Cord Type 16/3 SJTOW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
Product Name	Safety Yellow
Type	Hand Lamps
UPC	78678879528

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJTOW
Depth	101.60mm (4.000")
Duty	Commercial
Guard Included	Yes
Guard Type	Reflector, Screw Release

Height	381.00mm (15.000")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	Side
Packaging Type	Carton

This document was generated on Sep 13, 2025