



Part Number : [190120033](#)

Product Description : Avikrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 10-12 AWG, Yellow Insulator, Loose

Series Number : 19012

Status : Active

Product Category : Quick Disconnects

Engineering Number : C-8303

Documents & Resources

Drawings

[Drawing 190120033_sd.pdf](#)

[Packaging Design Drawing PK-19902-001-001.pdf](#)

Specifications


[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19902-014-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19012
Description	Avikrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 10-12 AWG, Yellow Insulator, Loose
Product Family	Standard Quick-Disconnect Terminals
Product Name	Avikrimp
Type	Quick Disconnect
UPC	822350942492

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	300V AC
-------------------	---------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Partial
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.919/g

Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	105°C
Wire Insulation Diameter	5.71mm max.
Wire Size (AWG)	10, 12

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640016400</u>

This document was generated on Jul 28, 2024