



Part Number : [1301020253](#)

Product Description : Safeway Phenolic Hand Lamp with 100W, Screw Release Guard with Reflector, with Switch, Cord Type 16/3 SJTOW, Cord Length 7.62m (25.0')

Series Number : 130102

Status : Active

Product Category : Lamps and Lights

Engineering Number : 271SA163



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130102
Description	Safeway Phenolic Hand Lamp with 100W, Screw Release Guard with Reflector, with Switch, Cord Type 16/3 SJTOW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
Product Name	Safety Yellow
Type	Hand Lamps
UPC	78678879524

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJTOW
Depth	101.60mm (4.000")
Duty	Commercial
Guard Included	Yes
Guard Type	Reflector, Screw Release
Height	381.00mm (15.000")
Lamp Type	A21
Length	N/A

Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 17, 2025