
FCI CONFIDENTIAL

FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.



TECHNICAL SPECIFICATION

CONTACT MATERIAL	:	COPPER ALLOY
CONTACT PLATING	:	GOLD OVER NICKEL
OPERATING CURRENT	:	7.5 A PER CONTACT
CONTACT RESISTANCE	:	≤7.3mΩ
TERMINATION	:	CRIMP
WIRE SIZE	:	AWG 20 TO 24 MAX

PACKING : 2000 PIECES SEALED TO A PLASTIC COVER IN A BOX

FCI PART NUMBER: 86303020A
MIL PART NUMBER: M39029/64369

mat'l. code: See Notes	surface ISO 1302	tolerance ISO 406 ISO 1101	projection
	tolerances unless otherwise specified		
angles: –	linear: .0±0.1		MM
	linear: .00±0.1		scale 10:1
	linear: –		

ltr	ecn no	dr	date
A	098-09-14	AB	2014-09-04

dr	ALIAS BABU	2014-09-04
engr	ALIAS BABU	2014-09-04
chr	MITHUN PAUL	2014-09-04
appd	BIJU K PAUL	2014-09-04

sheet index	revision: A
	sheet: 1

product family: DM

title: MALE CRIMP CONTACTS FOR DM 20/24 AWG

dwg no: C-DSUB-0207 | sheet 1 of 1 | size: A4

type: CUSTOMER Drawing

form: A4

Downloaded from Arrow.com.