








PRODUCT NUMBER

SEE PART NO. TABLE

2P3P

NOTES:

1. MATERIAL: NYLON 66, UL 94V-0.
2. THIS HSG IS USED WITH FCI CRIMP TERMINAL 10142959.
3. THIS RECEPTACLE MATES WITH FCI PLUG 10142994.
4. PRODUCT SPECIFICATION: GS-12-1408.
5. PACKAGE SPECIFICATION: GS-14-2573.
6. PART NUMBER SCHEME:
10142958- XX 0 XX LF

COLOR CODE:

- 00: NATURAL
- 01: BLACK
- 02: BROWN
- 03: RED
- 04: ORANGE
- 05: YELLOW
- 06: GREEN
- 07: BLUE
- 08: PURPLE
- 09: GREY
- 10: WHITE
- 11: MILKY YELLOW
- 12: BRICK RED
- 13: MILKY WHITE

PIN COUNTS: 02~20

POS	A	B	C	POS	A	B	C
2	2.5	5.64	7.3	12	27.5	30.64	32.3
3	5.0	8.14	9.8	13	30.0	33.14	34.8
4	7.5	10.64	12.3	14	32.5	35.64	37.3
5	10.0	13.14	14.8	15	35.0	38.14	39.8
6	12.5	15.64	17.3	16	37.5	40.64	42.3
7	15.0	18.14	19.8	17	40.0	43.14	44.8
8	17.5	20.64	22.3	18	42.5	45.64	47.3
9	20.0	23.14	24.8	19	45.0	48.14	49.8
10	22.5	25.64	27.3	20	47.5	50.64	52.3
11	25.0	28.14	29.8				

mat'l. code				surface		tolerance	projection	product family					
ltr	ecn	no	dr	date	tolerances unless otherwise specified			WTB					
A			TONY		2017-03-01		angles	.X±0.30					
							linear	.XX±0.20					
					0°±5°			.XXX±0.10					
						dr	TONY_LEN	2017-03-01					
						engr	TONY_LEN	2017-03-01					
						chr	ZK_HU	2017-03-01					
						appd	TIM_YAO	2017-03-01					
sheet	revision	A						dwg no	sheet 1 of 1	size			
index	sheet	1						10142958					
Amphenol FCi													
type Product Customer Drawing													