

Search within category

GO

BUY NOW

DESIGN / INSTALL



PLT4H-TL69

Pan-Ty® locking tie, light-heavy cross section, 14.6 (371mm) length, flame retardant nylon 6.6, ivory.

Specs	Packaging Details	Tools	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Nylon 6.6				
Application	General				
Color	Ivory				
Cross Section	Light-Heavy				
Locking Style	Locking				
Continuous Use Temperature Range	-76°F (-60°C) - 212°F (100°C)				
Plenum-Rated	No				
Tool	GTHE, GS4H, GS4EH, PTH, STH2, ST3EH				
Length In (mm)	14.6 (371)				
Thickness In (mm)	0.075 (1.9)				
Bundle Diameter Range In. (mm)	0.19 (4.8) - 4.00 (102)				
CE Compliant	Yes				
CSA Certified	Yes				
Mil. Std. Part Number	NA				
UL 62275 Compliant (Type 1, 11)	Yes				
UL 62275 Compliant (Type 2, 21)	No				
UL Listed (File #E56854)	No				
UL Recognized (File #E56854)	Yes				
Environment	Indoor				
Installation Temperature	-4°F (-20°C) - 32°F (0°C)				
Min. Loop Tensile Strength (Lbs.)	120				
Min. Loop Tensile Strength (N)	534				
Operating Temperature	-76°F (-60°C) - 212°F (100°C)				
Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.				
Width In (mm)	0.30 (7.6)				
RoHS Compliancy Status	Compliant				
Min. Order Qty.	250				