

[Terminals & Splices](#) > [Splices](#)

SPLICE,STRATO-THERM, BUTT, HR, 4 AWG

✓ ACTIVE

STRATO-THERM |
SOLISTRAND STRATO-THERM SpliceTE Part # **1958509-1**
TE Internal #: **1958509-1**Product Type : **Splice**
Terminal & Splice Style : **Splice**
Wire Size (mm²): **16.8 – 26.7**
Sealable : **No**
Splice Features : **Sight Hole** Add to List ▾ | [Similar Products](#)

ORDER SAMPLES

[Compatible Parts & Tooling](#)

SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and
customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

SPLICE,STRATO-THERM, BUTT, HR, 4 AWG

 SPLICE,STRATO-THERM, BUTT, HR, 4 AWG

English

CAD Files

3D PDF

 3D_CVM_CVM_1958509-1_A.pdf 3D

Customer View Model

 ENG_CVM_CVM_1958509-1_A.2d_dxf.zip

English

 ENG_CVM_CVM_1958509-1_A.3d_igs.zip

English

 ENG_CVM_CVM_1958509-1_A.3d_stp.zip

English

Please review product documents or [contact us](#) for the latest agency approval
information. Please Note: Use the Product Drawing for all design activity.Product Type
FeaturesProduct Type : **Splice**Sealable : **No**Splice Type : **Butt Splice**Serrated : **Yes**



	Accessory Type : Splice Barrel Type : Closed Barrel Insulated : No
Configuration Features	Number of Serrations : 42
Body Features	Splice Features : Sight Hole Splice Material : Copper Plating Material : Nickel
Contact Features	Terminal & Splice Style : Splice Contact Plating Material : Nickel Contact Plating Thickness (µin): 300
Mechanical Attachment	Wire Insulation Support : Without
Dimensions	Wire Size (mm²): 16.8 – 26.7 Barrel Inside Diameter : 7.52 mm [.296 in] Wire Size (CMA): 33100 – 52600 Material Thickness : 1.78 mm [.070 in] Overall Length : 28.96 mm [1.14 in]
Usage Conditions	High Temperature Rating : 343 °C [650 °F]
Operation/Application	Heavy Duty : No
Industry Standards	Government Qualified : No
Packaging Features	Packaging Method : Loose Piece Packaging Quantity : 100
Other	Military Category : No
Statement of Compliance	Statement of Compliance pdf

Compatible Parts

[Contact Product Support](#)

Also in the Series | [SOLISTRAND STRATO-THERM Splice](#)



Splices (1)

Customers Also Bought



TE Part # 5-104893-5
50 50/50 GRID CABLE RECPT LF



TE Part # 322326
SPLICE, SOLIS PARA HT 22-16



TE Part # 323672
SPLICE, SOLIS PARA HT 12-10



TE Part # 104891-5
50 50/50 GRID CABLE RCPT COVER