
Part Number : 190580026
Product Description : Avikrimp Ring Tongue Terminal for 16-14 AWG,, Carton
Series Number : 19058
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : B-801-76HD



Documents and Resources

Drawings

190580026_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19058
Description	Avikrimp Ring Tongue Terminal for 16-14 AWG,, Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	Avikrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753059214

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	4.362/g
Packaging Type	Carton

Downloaded from Arrow.com.

Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	7/16" (M11)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.70mm max.
Wire Size (AWG)	14, 16
Wire Size mm^2	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm^2 (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010100
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640160036

Downloaded from Arrow.com.