



Part Number : [151350801](#)

Product Description : CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 100.00mm Length, 8 Circuits, Beige

Series Number : 15135

Status : Active

Product Category : Power and Signal Cable Assemblies




Documents and Resources

Drawings

[151350801_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|------------------------|---|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 15135 |
| Description | CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 100.00mm Length, 8 Circuits, Beige |
| Application | Signal, Wire-to-Board |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | CLIK-Mate-to-CLIK-Mate |
| Product Name | CLIK-Mate |
| Type | Discrete Wire Assembly |
| UPC | 191128160438 |

Electrical

| | |
|-------------------------------|------------------|
| Current - Maximum per Contact | 2.0A |
| Voltage - Maximum | 100V AC (RMS)/DC |

Physical

| | |
|---------------------------|--------------|
| Cable Length | 100.00mm |
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | Beige |
| Gender | Male-Male |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |

| | |
|--------------------------------|----------------------------------|
| Material - Plating Termination | Tin |
| Material - Resin | Polybutylene Terephthalate (PBT) |
| Net Weight | 3.802/g |
| Number of Rows | 1 |
| Overmolded | No |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.50mm |
| Plating min - Mating | 0.406µm |
| Plating min - Termination | 0.406µm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 1061 |
| Wire Size (AWG) | 24 |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|--|---------------|
| 1.50mm Pitch CLIK-Mate Bottom Entry Single Row PCB Receptacles | <u>503395</u> |
| 1.50mm Pitch CLIK-Mate Right-Angle Single Row PCB Receptacles | <u>503175</u> |
| 1.50mm Pitch CLIK-Mate Right-Angle Single Row PCB Receptacles | <u>502585</u> |
| 1.50mm Pitch CLIK-Mate Vertical Single Row PCB Receptacles | <u>503159</u> |
| 1.50mm Pitch CLIK-Mate Vertical Single Row PCB Receptacles | <u>502584</u> |

This document was generated on Apr 21, 2026