

Part Number : [444761111](#)

Product Description : Mini-Fit HCS Crimp Terminal, 20-18 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)

Series Number : 44476

Status : Not Recommended For New Design

Product Category : Crimp Terminals



Documents and Resources

Drawings

[444761111_sd.pdf](#)

Specifications

[PS-44476-001-001.pdf](#)

[55560008-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Not Recommended For New Design
Category	Crimp Terminals
Series	44476
Description	Mini-Fit HCS Crimp Terminal, 20-18 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)
Comments	High Current
Product Name	Mini-Fit
UPC	800755527827

Electrical

Current - Maximum per Contact	11.0A
-------------------------------	-------

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.200/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size (AWG)	18, 20
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	<u>11030044</u>
Extraction Tool for Mini-Fit HCS Terminals, 20-16 AWG	<u>638131200</u>
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 24-18 AWG	<u>638190901</u>
FineAdjust Applicator for 20-18 AWG and 24-18 AWG Wires with Insulation Diameter 1.90-2.30mm	<u>639015600</u>
FineAdjust Applicator for Insulation OD 1.40-1.70mm - 24-18 AWG	<u>639023900</u>
FineAdjust Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	<u>639024800</u>
FineAdjust Applicator for Insulation OD 2.30-2.60mm - 24-18 AWG	<u>639024900</u>
FineAdjust Applicator for Insulation OD 2.50-2.95mm, 24-18 AWG	<u>639047800</u>
FineAdjust Applicator for Insulation OD 1.65-2.05mm, 24-18 AWG	<u>639048000</u>
T2 Terminator for Insulation OD 1.90-2.30mm - 24-18 AWG	<u>639115600</u>
T2 Terminator for insulation OD 1.40-1.70mm - 24-18 AWG	<u>639123900</u>
T2 Terminator for insulation OD 2.50-2.95mm optimized for 18 AWG only	<u>639124800</u>
T2 Terminator for insulation OD 2.30-2.60mm - 24-18 AWG	<u>639124900</u>
T2 Terminator for Mini-Fit Crimp Terminals, 24-18 AWG with Large	<u>639147800</u>

Insulation ODs	
T2 Terminator for Mini-Fit Crimp Terminals, 24-18 AWG with Smaller Insulation ODs	<u>639148000</u>

This document was generated on Sep 10, 2026